

BACKREST RAIL

STATIONARY HINGED SUPPORT RAILS

NECESSARY FOR ALL



805.51.906

- c to c 650 - 750 mm adjustable on site
- 150 mm deep
- double-sided mounting
- backrest made of synthetic material in HEWI colours 98 (signal white), 92 (anthracite grey) and 90 (jet black)
- rails made of stainless steel, satin finish



805.51.907

- do.
- 230 mm deep



**805.51.926R
805.51.926L**

- c to c 650 - 750 mm adjustable on site
- 150 mm deep
- one-sided installation
- backrest made of synthetic material in HEWI colours 98 (signal white), 92 (anthracite grey) and 90 (jet black)
- rails made of stainless steel, satin finish




**805.51.927R
805.51.927L**

- do.
- 230 mm deep



Stainless steel, satin finish



**805.50.2...0
805.50.1...0 | rotatable**



BM17.2

For fixing on walls made of concrete (> C20/C25)
National technical approval number: ETA-11/0493

additionally: injection mortar (HEWI item No.: 200311)
or to be provided on site: injection mortar HIT-HY200A (Hilti)
extrusion tool HDM (Hilti)

BM10.2

For fixing on walls made of concrete (> C20/C25)

BM11.2

For fixing on walls made of concrete (> P2)

additionally:
injection mortar (HEWI item No.: 200266),
conical drill bit (HEWI item No.: 171041)
or to be provided on site:
injection mortar HIT-HY 270 (Hilti),
extrusion tool HDM (Hilti),
conical drill bit TE-C PB 22/100 (Hilti)

BM12.2

For fixing on lightweight walls with rear lining made of laminated timber boards (with waterproof bonding, at least 30 mm thick required, e.g. studs or prewall installation)

BM13.2

For fixing on lightweight walls with integrated steel plates (e.g. studs or pre wall installation)

BM18.2

For fixing on walls made of:

- solid bricks
- perforated calcium silicate block
- hollow concrete block
- vertically perforated bricks
- hollow lightweight concrete block
- lightweight aggregate concrete with open structure

National technical approval number: ETA-13/1036

additionally:
injection mortar (HEWI item No.: 200266)
or to be provided on site:
injection mortar HIT-HY 270 (Hilti),
extrusion tool HDM (Hilti)

Backrest rail cannot be combined with mobile versions.